# GRIMM **GRIMM**

## **EDM 180** ENVIRONMENTAL DUST MONITOR FOR APPROVED PM MEASUREMENTS

The GRIMM EDM 180 is the leading Automated Measuring System (AMS) for measuring particulate matter concentration ( $PM_{10}$ ,  $PM_{25}$ ) in ambient air.

This system offers outstanding features such as simultaneous PM measurements in 31 particle size channels, 0.1  $\mu$ g/m<sup>3</sup> resolution, and an isothermal inlet with an integrated Nafion dryer. The EDM 180 runs silently, requires low maintenance and can be validated on site using the field test kit together with our system diagnosis software.

The EDM 180 is the optimal solution for reliable environmental monitoring, e. g. automated PM measurements in environmental networks, epidemiological studies, urban and rural PM monitoring. The EDM 180 is in service of governmental networks and institutes in over 30 countries.

#### **FEATURES**

- certificates and approvals: EN, US-EPA, UK-MCERTS, CN-CMA; demonstration of equivalence in over 20 countries
- real-time measurement of PM<sub>10</sub>, PM<sub>2.5</sub>, PM<sub>1</sub>, total counts (TC), and particle number distribution
- fully automated monitoring system with remote access
- extremely energy-efficient, low maintenance, no consumables
- no loss of semi-volatile compounds
- no radioactive source, insensitive to vibrations (applicable also in vehicles)
- versatile data acquisition and communication (GSM data logger)
- self-test of all optical and pneumatic components for high quality standards
- rinsing air for protecting laser and detector in optical cell
- temperature and relative humidity sensors
- total inlet flow analyzed in optical cell
- excellent counting statistics and reproducibility at low and high dust concentrations



#### **APPLICATIONS**

- AMS for PM networks
- PM monitoring
- epidemiological studies
- monitoring of construction and mining sites

| PM <sub>10</sub> PM <sub>2.5</sub> | US EPA            | MCERTS                             | EN 12341                | EN 14907          |
|------------------------------------|-------------------|------------------------------------|-------------------------|-------------------|
| PM <sub>1</sub>                    | PM <sub>2.5</sub> | PM <sub>10</sub> PM <sub>2.5</sub> | <b>PM</b> <sub>10</sub> | PM <sub>2.5</sub> |

#### **SPECIFICATIONS**

| measured mass fractions | PM <sub>10</sub> , PM <sub>2.5</sub> , PM <sub>1</sub>   |
|-------------------------|--|
| optionally              | TC (Total Counts) and particle number for all size channels  |
| particle size range     | 0.25 - 32 μm   |
| size channels           | 31   |
| particle number         | 0 - 3 000 000 p/L  |
| reproducibility         | > 97% of total measuring range   |
| dust mass range         | 0 - 10 000 μg/m <sup>3</sup> (PM <sub>10</sub> ), 0 - 6 000 μg/m <sup>3</sup> (PM <sub>2.5</sub> ) |

#### **FUNCTION**

| detection principle optical    | light scattering at single particles;<br>detection volume aerodynamically focused, no border zone error                 |
|--------------------------------|---|
| optical cell                   | diode laser 660 nm  |
| detector                       | fast signal processing, 2 x 16 raw data channels  |
| time resolution                | selectable storage intervals: 6 s; 1, 5, 10, 15, 30, 60 min   |
| sample air flow rate           | 1.2 L/min, $\pm$ 3% constant due to self-regulation   |
| internal rinsing air flow rate | 0.4 L/min, protection for laser optics, reference air for self-test   |
| sampling inlet                 | isothermal humidity extraction via Nafion membrane,<br>sensor-controlled, without loss of semi-volatile compounds (SVC) |

### HANDLING

| operation                  | keypad or PC with GRIMM software or Hyper Terminal   |
|----------------------------|--|
| interfaces                 | RS-232 (GESYTEC)   |
| analog input               | 1 port (0 - 10 V) for auxiliary sensors  |
| power supply               | in: 230 V/50 Hz; optional 115 V/60 Hz; or 220 V/60 Hz  |
| power consumption          | 18 W standard, 104 W with Nafion dryer, 116 W maximum, I <sub>max</sub> : 1.4 A  |
| temperature range          | -20 to +50°C (-4 to 122°F), non-condensing   |
| absolute pressure range    | 900 - 1100 mbar;<br>adjustable sample flow rate at high altitudes over 2000 m  |
| weather protection housing | model <b>199</b> , stand-alone, fully air-conditioned, providing space for EDM180 and other 19" rack instruments (see Accessories) |
| dimensions (h x w x d)     | 26.6 x 48.3 x 36.4 cm (10.5 x 19 x 14.3 in) without sampling inlet (19" rack, 4 HU, extra 2 HU for rack adapter)                   |
| weight                     | 18 kg (39.7 lbs) without rack adapter and sampling pipe  |